




**Pushbutton switch 10 AX 250 V~with upright rocker, 2-gang
2-way switch, 2-gang**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 pure white glossy	2861 201	1/5	36.02	01	4010337065883
 pure white matt	2861 27	1/5	36.02	01	4010337053286
 anthracite	2861 28	1/5	36.49	11	4010337053293
 colour aluminium	2861 26	1/5	39.37	11	4010337053279
 stainless steel	2861 600	1/5	45.67	11	4010337021209

Technical data

Installation depth

- 2860 ...:	28 mm
- 2861 ...:	32 mm

Connection cross section

- For rigid and flexible conductors up to:	2.5 mm ²
--	---------------------

Rated output

- LEDi/CFLi:	100 W
--------------	-------

Notes

- Subject to availability.
