



Rocker switch insert 10 AX 250 V~ series switch



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3105 00	10/100	14.58	01	4010337038856
 without mounting claws	3815 00	10	14.58	01	4010337038863

Features

- Can also be used with 1-gang rocker.

⋮
⋮
⋮

- Shatter-proof thermoplastic base.

⋮
⋮

Technical data

Installation depth

- 3105 00: 32 mm
- 24 mm: 23 mm

Connection cross section

- For rigid and flexible conductors up to: 2.5 mm²

Rated output

- LEDi/CFLi: 100 W