



## Rocker switch insert 10 AX 250 V~ series switch



| Specification  | Order No. | Packing unit | PS | EAN           |
|--|-----------|--------------|----|---------------|
|  with mounting claws      | 3105 00   | 10/100       | 01 | 4010337038856 |
|  without mounting claws | 3815 00   | 10           | 01 | 4010337038863 |

### Technical data

#### Installation depth

|            |       |
|------------|-------|
| - 3105 00: | 32 mm |
| - 24 mm:   | 23 mm |

#### Connection cross section

|  |                     |
|--|---------------------|
| - For rigid and flexible conductors up to: | 2.5 mm <sup>2</sup> |
|--|---------------------|

#### Rated output

|              |       |
|--------------|-------|
| - LEDi/CFLi: | 100 W |
|--------------|-------|