



## Rocker switch insert 10 AX 250 V~ 2-way switch, 2-pole



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3109 00	1	27.85	01	4010337038993
 without mounting claws	3819 00	1	27.85	01	4010337039068

### Features

- 
- 
- Shatter-proof thermoplastic base.
- 

### Technical data

Installation depth:	32 mm
Installation depth:	24 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm <sup>2</sup>
Rated output	
- LED/CFLi:	100 W

### Notes

- Can also be connected to be illuminated.