



Rocker switch insert 10 AX 250 V~ 2-way switch, 2-pole



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3109 00	1	27.85	01	4010337038993
 without mounting claws	3819 00	1	27.85	01	4010337039068

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

Technical data

Installation depth:	32 mm
Installation depth:	24 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm²
Rated output	
- LEDi/CFLi:	100 W

Notes

- Can also be connected to be illuminated.