




**Rocker indicator switch insert 10 AX 250 V~  
with orange LED lighting element element 230 V~  
circuit breaker, 2-pole**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3112 00	10	32.69	01	4010337038696
 without mounting claws	3822 00	1	32.69	01	4010337038702

#### Technical data

Installation depth

- 3112 00: 32 mm
- 3822 00: 23 mm

Connection cross section

- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>

Rated output

- LEDi/CFLi: 100 W

#### Notes

- Can also be connected to be illuminated by rotating the LED insert by 180°.