




**Rocker indicator switch insert 10 AX 250 V~  
with orange LED lighting element element 230 V~  
circuit breaker, 2-pole**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3112 00	10	33.73	01	4010337038696
 without mounting claws	3822 00	1	33.73	01	4010337038702

## Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.

## Technical data

### Installation depth

- 3112 00: 32 mm
- 3822 00: 23 mm

### Connection cross section

- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>

### Rated output

- LEDi/CFLi: 100 W

## Notes

- Can also be connected to be illuminated by rotating the LED insert by 180°.
- 

## Scope of supply

- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.
-