




**Rocker indicator switch insert 10 AX 250 V~
with orange LED lighting element 230 V~
universal off/2-way switch**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3116 00	10/100	23.14	01	4010337038955
 without mounting claws	3826 00	10	23.14	01	4010337039037

Technical data

Installation depth

- 3116 00:	32 mm
- 3826 00:	23 mm

Connection cross section

- For rigid and flexible conductors up to:	2.5 mm ²
--	---------------------

Rated output

- LEDi/CFLi:	100 W
--------------	-------

Notes

- Can also be connected to be illuminated.

Scope of supply

- Orange LED lighting element 230 V~ 0.5 mA is included in the scope of supply.