




**Rocker indicator switch insert 10 AX 250 V~
with orange LED lighting element 230 V~
universal off/2-way switch**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3116 00	10/100	23.88	01	4010337038955
 without mounting claws	3826 00	10	23.88	01	4010337039037

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

Technical data

Installation depth

- 3116 00: 32 mm
- 3826 00: 23 mm

Connection cross section

- For rigid and flexible conductors up to: 2.5 mm²

Rated output

- LEDi/CFLi: 100 W

Notes

- Can also be connected to be illuminated.
-

Scope of supply

- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.
-