




**Rocker indicator switch insert 10 AX 250 V~  
with orange LED lighting element 230 V~  
universal off/2-way switch**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3116 00	10/100	23.14	01	4010337038955
 without mounting claws	3826 00	10	23.14	01	4010337039037

#### Technical data

Installation depth

- 3116 00: 32 mm
- 3826 00: 23 mm

Connection cross section

- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>

Rated output

- LEDi/CFLi: 100 W

#### Notes

- Can also be connected to be illuminated.