


**Rocker indicator switch 10 AX 250 V~
with mounting plate
and orange LED lighting element 230 V~**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 pure white	3116 13	10	29.26	13	4010337112471

Features

- With LED lighting element.
- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic[®] or would that then be polycarbonate.

Technical data

- Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²
- Rated output
- LEDi/CFLi: 100 W

Notes

- Can also be connected to be illuminated.

Scope of supply

- All devices are delivered including mounting plate, cable and duct entries.
- Orange LED lighting element 230 V~ 0.5 mA is included in the scope of supply.