




Pushbutton indicator switch insert 10 AX 250 V~ with orange LED lighting element 230 V~ circuit breaker, 2-pole



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3122 00	1	36.56	01	4010337038726
 without mounting claws	3842 00	1	36.56	01	4010337064381

Features

-
-
-
- Shatter-proof thermoplastic base.
-

Technical data

Installation depth	
- 3122 00:	32 mm
- 3842 00:	23 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm ²
Rated output	
- LEDi/CFLi:	100 W

Notes

- Can also be connected to be illuminated by rotating the LED insert by 180°.

Scope of supply

- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.
