



**Pushbutton switch insert 10 AX 250 V~
series switch, without rocker, 2-gang**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3125 00	10	21.59	01	4010337038894
 without mounting claws	3835 00	1	21.59	01	4010337038924

Technical data

Installation depth

- 3125 00:	32 mm
- 3835 00:	23 mm

Connection cross section

- For rigid and flexible conductors up to:	2.5 mm ²
--	---------------------

Rated output

- LEDi/CFLi:	100 W
--------------	-------