



Insert pushbutton switch 10 AX 250 V~universal off/2-way switch



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3126 00	10/100	12.70	01	4010337039020
 without mounting claws	3836 00	10	12.70	01	4010337038962

Features

- In contrast to rocker switches, the rockers on momentary-action switches always return to their original position after each actuation.
- The resulting standardised rocker position enables a tidy and high-quality appearance of the electrical installation.
- The aesthetics are significantly enhanced, especially with multiple combinations, for example with several switches in one frame.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

Technical data

Installation depth

- 3126 00: 32 mm
- 3836 00: 23 mm

Connection cross section

- For rigid and flexible conductors up to: 2.5 mm²

Rated output

- LEDi/CFLi: 100 W

Notes

- Can also be connected to be illuminated.
-