




Insert pushbutton switch 10 AX 250 V~intermediate switch



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3127 00	10	25.21	01	4010337039198
 without mounting claws	3837 00	1	18.92	01	4010337064404

Technical data

Installation depth

- 3127 00:	32 mm
- 3837 00:	23 mm

Connection cross section

- For rigid and flexible conductors up to:	2.5 mm ²
--	---------------------

Rated output

- LEDi/CFLi:	100 W
--------------	-------

Notes

- Can also be connected to be illuminated.