




Insert pushbutton switch 10 AX 250 V~2-way switch, 2-gang



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3128 00	10	30.06	01	4010337039075
 without mounting claws	3838 00	1	30.06	01	4010337064411

Features

- Can also be used with 1-gang rocker.

⋮
⋮
⋮
⋮
⋮

- Shatter-proof thermoplastic base.

⋮

Technical data

Installation depth: 32 mm

Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²

Rated output
- LEDi/CFLi: 100 W