




**Pushbutton switch insert 10 AX 250 V~
2-way switch, 2-gang, without rocker**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3128 00	10	33.82	01	4010337039075
 without mounting claws	3838 00	1	33.82	01	4010337064411

Technical data

Installation depth:	32 mm
Connection cross section - For rigid and flexible conductors up to:	2.5 mm ²
Rated output - LEDi/CFLi:	100 W