



**Pushbutton indicator switch insert 10 AX 250 V~
with orange LED lighting element 230 V~
series switch**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3135 00	1	35.57	01	4010337038917
 without mounting claws	3845 00	1	35.57	01	4010337064398

Features

- Can also be used with 1-gang rocker.

-
-
-
-
-
-

- Shatter-proof thermoplastic base.

-

Technical data

Installation depth

- 3135 00: 32 mm
- 3845 00: 23 mm

Rated output

- LEDi/CFLi: 100 W

Scope of supply

- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.