



Rocker button insert, 4-gang 10 A 250 V~ NO contact, 1-pole



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3147 00	10	27.63	01	4010337038832
 without mounting claws	3867 00	1	27.63	01	4010337064855

Features

- Can also be used as 2-gang NO contact with 1-gang rocker.

⋮
⋮
⋮
⋮
⋮

- Shatter-proof thermoplastic base.

⋮

Technical data

Installation depth: 32 mm

Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²

Notes

- For deep device boxes.