



Rocker button insert 10 A 250 V~ NO contact, 1-pole with sep. signal contact



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--|-----------|--------------|------------------------|----|---------------|
|  with mounting claws | 3152 00 | 10 | 15.30 | 01 | 4010337038801 |
|  without mounting claws | 3872 00 | 1 | 15.30 | 01 | 4010337064633 |

Technical data

Installation depth

- 3152 00: 32 mm
- 3872 00: 23 mm

Connection cross section

- For rigid and flexible conductors up to: 2.5 mm²

Notes

- Can also be connected to be illuminated.