


Rocker button insert 10 A 250 V~ 2-way momentary contact, 2-gang



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3155 00	10	25.78	01	4010337039112
 without mounting claws	3875 00	10	25.78	01	4010337064688

Features

- Can also be used with 1-gang rocker.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

Technical data

Installation depth: 32 mm

Connection cross section

- For rigid and flexible conductors up to: 2.5 mm²