



## Rocker button insert 10 A 250 V~ 2-way momentary contact, 1-pole



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3156 00	10	10.72	01	4010337039099
 without mounting claws	3876 00	10/100	10.72	01	4010337064695

### Technical data

#### Installation depth

- 3156 00:	32 mm
- 3876 00:	23 mm

#### Connection cross section

- For rigid and flexible conductors up to:	2.5 mm <sup>2</sup>
--	---------------------

### Notes

- Can also be connected to be illuminated.