



Blind rocker switch insert 10 A 250 V~



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--|-----------|--------------|------------------------|----|---------------|
|  with mounting claws | 3159 00 | 10/100 | 25.14 | 01 | 4010337039211 |
|  without mounting claws | 3879 00 | 10 | 25.14 | 01 | 4010337064428 |

Features

- With block to prevent both sides from being switched on.
- Locked both electrically and mechanically.

Technical data

Installation depth

- 3159 00: 32 mm
- 3879 00: 23 mm

Connection cross section

- For rigid and flexible conductors up to: 2.5 mm²

Notes

- Suitable for use as an auxiliary unit for the blind controller insert with auxiliary input.