


**Rocker indicator switch 16 AX 250 V~  
with inscription space and  
orange LED lighting element 230 V~**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 grey	3186 30	1	40.44	14	4010337125945

## Features

- With orange LED lighting element.
- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.

## Technical data

- Connection cross section
- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>
- Rated output
- LEDi/CFLi: 100 W

## Notes

- Can also be connected to be illuminated.

## Scope of supply

- Inscription label "Heating On/Off", "VERWARMING AAN/UIT" is enclosed.
- Cable entry 2-gang (twin entry) is enclosed.
- Orange LED lighting element 230 V~ 0.5 mA is included in the scope of supply.