










Rocker with symbol Bell



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	3286 01	1	5.25	01	4010337039723
 pure white glossy	3286 03	10	5.25	01	4010337039730
 pure white matt	3286 27	10	5.25	01	4010337039754
 anthracite	3286 28	10	5.71	11	4010337039761
 colour aluminium	3286 26	1	8.63	11	4010337039747
 black matt	3286 005	5	8.63	11	4010337067870
 grey matt	3286 015	1	8.63	11	4010337110477
 stainless steel	3286 600	1	15.23	11	4010337045151

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
 - Quick mounting (3.5 turns per mounting claw).
 - Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-