









Rocker with inscription space



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	3299 01	1	7.41	01	4010337039471
 pure white glossy	3299 03	10	7.41	01	4010337039488
 pure white matt	3299 27	1	7.41	01	4010337039501
 anthracite	3299 28	1	7.88	11	4010337039518
 colour aluminium	3299 26	1	10.80	11	4010337039495
 black matt	3299 005	1	10.80	11	4010337066859
 grey matt	3299 015	1	10.80	11	4010337110545
 stainless steel	3299 600	1/5	17.38	11	4010337044956

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

Scope of supply

- Blank inscription label enclosed.
 - Inscription labels with symbols "Light", "Call button" and "Door" are enclosed.
-