

Upright rocker with control window



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 pure white glossy	3490 66	1	11.56	13	4010337066774
 anthracite	3490 67	1	14.92	13	4010337066842
 colour aluminium	3490 65	1	14.92	13	4010337066767

Features

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Water-protected flush-mounted IP44