








Upright rocker, 2-gang



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 pure white glossy	3495 03	1	7.12	01	4010337065647
 pure white matt	3495 27	10	7.12	01	4010337065661
 anthracite	3495 28	1	7.64	11	4010337065678
 colour aluminium	3495 26	1	10.60	11	4010337065654
 black matt	3495 005	1	10.60	11	4010337065630
 grey matt	3495 015	1	10.60	11	4010337110606
 stainless steel	3495 600	1/5	17.12	11	4010337065685

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).

- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-