

Rocker with control window and symbol Light



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	3674 01	1	6.54	01	4010337041870
 pure white glossy	3674 03	10	6.54	01	4010337041887
 pure white matt	3674 27	10	6.54	01	4010337041993
 anthracite	3674 28	10	7.03	11	4010337042099
 colour aluminium	3674 26	1	9.97	11	4010337041894
 black matt	3674 005	1	9.97	11	4010337067221
 grey matt	3674 015	1	9.97	11	4010337110583

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.

- Quick mounting (3.5 turns per mounting claw).
 - Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-