




## Rocker switch and rocker button insert 10 A 250 V~ 2-way switch / 2-way momentary contact



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 with mounting claws	3139 00	10	24.98	01	4010337039136
 without mounting claws	3869 00	1	24.98	01	4010337064565

### Features

- Rocker switch and button in which the left rocker is laid out as a switch and the right rocker is laid out as a push button.
- For switching and colour control of an LED orientation light.
- For controlling motion detectors manually.
- For activating dimmer auxiliary units.
- For controlling switched lighting.

### Technical data

Installation depth:	32 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm <sup>2</sup>
Rated output	
- LEDi/CFLi:	100 W