









**SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus), without mounting claws  
Screw terminals**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	4383 01	1/5	9.50	01	4010337093633
 pure white glossy	4383 03	1/5	9.50	01	4010337093657
 pure white matt	4383 27	1/5	9.50	01	4010337108450
 anthracite	4383 28	1/5	10.62	11	4010337093671
 colour aluminium	4383 26	1/5	14.68	11	4010337093664
 black matt	4383 005	1/5	14.68	11	4010337093626
 grey matt	4383 015	1/5	14.68	11	4010337093640
 stainless steel	4383 600	1/5	21.92	11	4010337093688

## Features

- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
  - Low installation depth.
  - Large, ergonomically shaped release levers.
  - Sturdy earth bar with solid earthing fingers.
  - Sturdy and corrosion-resistant steel support ring.
  - Shatter-proof thermoplastic base.
- 

## Technical data

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>
Ambient temperature - increased contact protection:	0°C to +45°C

---

## Notes

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
  - Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-