








**Danish socket outlet 16 A 250 V~
107-2-D1, DK 1-1b with increased contact protection (Safety Plus)
System 55**



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	4422 01	1/5	19.87	01	4010337092308
 pure white glossy	4422 03	1/5	19.87	01	4010337092322
 pure white matt	4422 27	1/5	19.87	01	4010337092346
 anthracite	4422 28	1/5	21.03	11	4010337092353
 colour aluminium	4422 26	1/5	25.25	11	4010337092339
 black matt	4422 005	1/5	25.25	11	4010337092292
 grey matt	4422 015	1/5	25.25	11	4010337092315

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
 - Quick mounting (approx. 3.5 turns per mounting claw).
 - Expanding claws in the housing.
 - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
 - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
 - Low installation depth.
 - Large, ergonomically shaped release levers.
 - Sturdy earth bar with solid earthing fingers.
 - Sturdy and corrosion-resistant steel support ring.
 - Shatter-proof thermoplastic base.
-

Technical data

Installation depth:	31 mm
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²

Notes

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-