


Power supply DC 12 V 2 A



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 DRA	5319 00	1	67.47	42	4010337774037

Features

- Power supply DC 12 V for the eNet server, eNet wireless receiver module and external camera.

Technical data

Rated voltage
- Primary: AC 100 to 240 V, 50/60 Hz
- Secondary: DC 12 to 14 V

Rated current
- Secondary: 2 A

Leakage current: max. 250 µA

Ambient temperature: -10 °C to +50 °C

Dimensions

Modular width (MW): 2