


eNet Radio remote control, 2-gang



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|-----------------------------------------------------------------------------------------------|-----------|--------------|------------------------|----|---------------|
|  anthracite | 5352 10 | 1 | 55.67 | 42 | 4010337774082 |

Features

- The eNet wireless transmitters send switching, dimming and blind motion commands to corresponding eNet wireless receivers.
- Two buttons belong to each channel.
- Each pair of buttons can be set as channel or scene function.
- Status LED.
- Battery-operated device.

Can be set with eNet server:

- Fully encrypted wireless transmission (AES CCM) from eNet Server software version 2.0.
- Signalling of the transmission status can be switched off.
- Operation locks.
- All-On or All-Off scenes, threshold value scenes, and individual scenes can be configured.
- Configuration of scene button using eNet SMART HOME App (if-then rules) to trigger actions, scenes and timers.
- Device software update.

Technical data

| | |
|----------------------|-----------------|
| Ambient temperature: | -5 °C to +45 °C |
| Wireless frequency: | 868.3 MHz |
| Range (free field): | approx. 100 m |
| Rated voltage: | DC 3 V |
| Battery | |
| - Type: | CR 2450N |
| - UN no.: | 3091 |

Notes

- Batteries are consumables and must be replaced regularly. Please observe the regulations on the disposal of used batteries.

Scope of supply

- Batteries are included in the scope of supply.

Dimensions in mm

B 40,5

H 55

T 15
