


## eNet wireless hand-held transmitter, 4-gang



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 anthracite	5354 10	1	69.60	42	4010337774099

### Features

- The eNet wireless transmitters send switching, dimming and blind motion commands to corresponding eNet wireless receivers.
- Two buttons belong to each channel.
- Each pair of buttons can be set as channel or scene function.
- Status LED.
- Battery-operated device.

Can be set with eNet server:

- Fully encrypted wireless transmission (AES CCM) from eNet Server software version 2.0.
- Signalling of the transmission status can be switched off.
- Operation locks.
- All-On or All-Off scenes, threshold value scenes, and individual scenes can be configured.
- Configuration of scene button using eNet SMART HOME App (if-then rules) to trigger actions, scenes and timers.
- Device software update.

### Technical data

Ambient temperature:	-5 °C to +45 °C
Wireless frequency:	868.3 MHz
Range (free field):	approx. 100 m
Rated voltage:	DC 3 V
Battery	
- Type:	CR 2450N
- UN no.:	3091

## Notes

- Batteries are consumables and must be replaced regularly. Please observe the regulations on the disposal of used batteries.

---

## Scope of supply

- Batteries are included in the scope of supply.

---

## Dimensions in mm

B 53

H 93

T 15,5

---