










## System 3000 operating top unit arrow symbols



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 cream white glossy	5361 01	1/5	28.57	02	4010337027270
 pure white glossy	5361 03	1/5	28.57	02	4010337027287
 pure white matt	5361 27	1/5	28.57	02	4010337027300
 anthracite	5361 28	1/5	31.16	02	4010337027317
 colour aluminium	5361 26	1/5	35.27	02	4010337027294
 black matt	5361 005	1/5	35.27	02	4010337037477
 grey matt	5361 015	1/5	35.27	02	4010337087212
 stainless steel	5361 600	1/5	42.71	02	4010337027324

### Technical data

Ambient temperature: -20°C to +45°C