









System 3000 blind timer and timer Display



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|---|-----------|--------------|------------------------|----|---------------|
|  cream white glossy | 5366 01 | 1/5 | 87.64 | 02 | 4010337027430 |
|  pure white glossy | 5366 03 | 1/5 | 87.64 | 02 | 4010337027447 |
|  pure white matt | 5366 27 | 1/5 | 87.64 | 02 | 4010337027461 |
|  anthracite | 5366 28 | 1/5 | 90.18 | 02 | 4010337027478 |
|  colour aluminium | 5366 26 | 1/5 | 94.12 | 02 | 4010337027454 |
|  black matt | 5366 005 | 1/5 | 94.12 | 02 | 4010337037484 |
|  grey matt | 5366 015 | 1/5 | 94.12 | 02 | 4010337087243 |
|  stainless steel (lacquered) | 5366 600 | 1/5 | 101.34 | 02 | 4010337027485 |

Features

- Operation via capacitive sensor surface.
- Fast programming for adopting the current time as the programmed movement time/switching time.
- Automatic summer/winter time switchover, deactivatable.
- Switching at sunrise or sunset (astro function) adjustable for 18 countries.
- Astro time for sunrise and sunset can be individually adjusted by ± 2 hours.
- The blocking function blocks operation of the auxiliary unit and deactivates automatic mode.
- The display turns off after 2 minutes, permanent display of time is possible.
- Programming one raising and one lowering time or two switch-on and switch-off times for weekdays (Mon-Fri) and for the weekend (Sat+Sun).

Technical data

Accuracy

- Per month: ± 10 s

Power reserve: approx. 4 h

Ambient temperature: -5°C to $+45^{\circ}\text{C}$
