









## System 3000 blind timer and timer Display



| Specification   | Order No. | Packing unit | PS | EAN           |
|---|-----------|--------------|----|---------------|
|  cream white glossy            | 5366 01   | 1/5          | 02 | 4010337027430 |
|  pure white glossy           | 5366 03   | 1/5          | 02 | 4010337027447 |
|  pure white matt             | 5366 27   | 1/5          | 02 | 4010337027461 |
|  anthracite                  | 5366 28   | 1/5          | 02 | 4010337027478 |
|  colour aluminium            | 5366 26   | 1/5          | 02 | 4010337027454 |
|  black matt                  | 5366 005  | 1/5          | 02 | 4010337037484 |
|  grey matt                   | 5366 015  | 1/5          | 02 | 4010337087243 |
|  stainless steel (lacquered) | 5366 600  | 1/5          | 02 | 4010337027485 |

## Features

- Operation via capacitive sensor surface.
- Fast programming for adopting the current time as the programmed movement time/switching time.
- Automatic summer/winter time switchover, deactivatable.
- Switching at sunrise or sunset (astro function) adjustable for 18 countries.
- Astro time for sunrise and sunset can be individually adjusted by  $\pm 2$  hours.
- The blocking function blocks operation of the auxiliary unit and deactivates automatic mode.
- The display turns off after 2 minutes, permanent display of time is possible.
- Programming one raising and one lowering time or two switch-on and switch-off times for weekdays (Mon-Fri) and for the weekend (Sat+Sun).

---

## Technical data

### Accuracy

- Per month:  $\pm 10$  s

Power reserve: approx. 4 h

Ambient temperature:  $-5^{\circ}\text{C}$  to  $+45^{\circ}\text{C}$

---