



## BNC insert, 2-gang Crimp connection



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 pure white glossy	5630 03	1/5	41.29	01	4010337460251
 black matt	5630 10	1/5	41.29	01	4010337460268

### Technical data

Wave impedance:	50 Ω
Installation depth:	25 mm

### Notes

- Not suitable for mounting frames with hinged covers.
- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40