




WBT-0710 Cu nextgen™ insert
Cable lug/solder termination



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 5665 01 | 1 | 01 | 4010337461449 |
|  pure white glossy | 5665 03 | 1 | 01 | 4010337461456 |
|  black matt | 5665 10 | 1 | 01 | 4010337461463 |

Technical data

Connection cross section

- maximum: 1 x 10 mm² (7 AWG)
- minimum: 1 x 4 mm² (11 AWG)

Notes

- Not suitable for mounting frames with hinged covers.
- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40