




HDMI, USB 3.0 type A and mini jack 3.5 mm insert
HDMI+USB coupler, breakout cable mini jack



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	5680 01	1	01	4010337461906
 pure white glossy	5680 03	1	01	4010337461913
 black matt	5680 10	1	01	4010337461920

Technical data

Installation depth	
- Gender changer:	mind. 39 mm
- Breakout cable:	mind. 51 mm
Length of the breakout cable:	200 mm

Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40