



## USB 3.0 type A insert Breakout cable



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 pure white glossy	5683 03	1	34.68	01	4010337462002
 black matt	5683 10	1	34.68	01	4010337462026

### Technical data

Installation depth	
- Breakout cable:	mind. 46 mm
Length of the breakout cable:	200 mm

### Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40