



USB 3.0 type A insert, 2-gang Gender changer



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 pure white glossy	5684 03	1	41.88	01	4010337462064
 black matt	5684 10	1	41.88	01	4010337462071

Technical data

Installation depth
- Gender changer: mind. 20 mm

Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40