




USB 3.0 type A insert, 2-gang Breakout cable



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 5685 01 | 1 | 01 | 4010337462088 |
|  pure white glossy | 5685 03 | 1 | 01 | 4010337462095 |
|  black matt | 5685 10 | 1 | 01 | 4010337462101 |

Technical data

| | |
|-------------------------------|-------------|
| Installation depth | |
| - Breakout cable: | mind. 46 mm |
| Length of the breakout cable: | 200 mm |

Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40