




## Modular jack RJ45 Cat.6A 10 Gbit Ethernet insert Gender changer



| Specification   | Order No. | Packing unit | PS | EAN           |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 5695 01   | 1/5          | 01 | 4010337463313 |
|  pure white glossy | 5695 03   | 1/5          | 01 | 4010337463337 |
|  black matt        | 5695 10   | 1/5          | 01 | 4010337463344 |

### Technical data

Installation depth  
- Gender changer: mind. 24 mm

### Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40