



**Modular Jack RJ45 cat.6A 10 Gbit Ethernet insert and SAT F jack
Gender changer, SAT F, insulation displacement connector, modular jack**



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--|-----------|--------------|------------------------|----|---------------|
|  pure white glossy | 5697 03 | 1/5 | 47.21 | 01 | 4010337463399 |
|  black matt | 5697 10 | 1/5 | 47.21 | 01 | 4010337463405 |

Technical data

| | |
|--------------------------|---------------|
| Installation depth: | 35 mm |
| Wave impedance for SAT: | 75 Ω |
| For internal conductors: | Ø 0.6 to 1 mm |

Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40