




Modular jack RJ45 Cat.6A 10 Gbit Ethernet insert, 4-gang Insulation displacement connectors



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	5699 01	1	01	4010337463450
 pure white glossy	5699 03	1	01	4010337463474
 black matt	5699 10	1	01	4010337463481

Technical data

Installation depth

- Insulation displacement connectors: 35 mm

Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40