

Interruptor pulsador 10 AX de 250 V~con tecla basculante recta
Interruptor en cruz



Especificación	Ref.	UE	SP	EAN
 blanco brillante	0123 201	1/5	01	4010337052708
 blanco mate	0123 27	1/5	01	4010337029342
 antracita	0123 28	1/5	11	4010337029366
 color aluminio	0123 26	1	11	4010337029359
 negro mate	0123 005	1	11	4010337037996
 gris mate	0123 015	1	11	4010337077114
 acero inoxidable	0123 600	1	11	4010337021254

Datos técnicos

Profundidad de instalación:	28 mm
Sección de conexión - para conductores rígidos y flexibles de hasta:	2,5 mm²
Potencia nominal - LEDi/ CFLi:	100 W

