

Pulsador 10 AX 250 V~ con tecla basculante recta
Contacto inversor, 1 polo



Especificación	Ref.	UE	SP	EAN
 blanco brillante	0130 201	1/5	01	4010337066064
 blanco mate	0130 27	1/5	01	4010337029434
 antracita	0130 28	1/5	11	4010337029458
 color aluminio	0130 26	1/5	11	4010337029441
 negro mate	0130 005	1/5	11	4010337037910
 gris mate	0130 015	1/5	11	4010337077183
 acero inoxidable	0130 600	1/5	11	4010337035947

Datos técnicos

Profundidad de instalación: 28 mm

Sección de conexión
- para conductores rígidos y flexibles de hasta: 2,5 mm²