







Marco cobertor Gira E2 antracita



| Especificación | Ref. | UE | SP | EAN |
|--|---------|--------|----|---------------|
|  1 elemento | 0211 23 | 10/100 | 11 | 4010337211235 |
|  1,5 elementos | 1001 23 | 10 | 11 | 4010337881339 |
|  2 elementos | 0212 23 | 10/100 | 11 | 4010337212232 |
|  2 elementos sin listón central | 1002 23 | 10 | 11 | 4010337002239 |
|  3 elementos | 0213 23 | 1/5 | 11 | 4010337213239 |
|  4 elementos | 0214 23 | 1/5 | 11 | 4010337214236 |
|  5 elementos | 0215 23 | 1 | 11 | 4010337215233 |

Notes

- También indicado para instalaciones en superficie.
- Marco cobertor (de 1 a 5 elementos) en combinación con el juego de juntas, también apropiado para la instalación empotrada IP44 protegida del agua.